

# SMC

PRESS ACTIVE SPLITTER





## PINANSON SMC PRESS ACTIVE SPLITTER

In a room where a signal must be distributed to the press, a sound technician processes the input from a console. It is needed that all the press, have the same signal trouble free, non of them must interfere in the others, in a moment the output signal must be turned up for a specific press group and the signal level of each press group must be tested:

**OUR SMC SPLITTER IS THE BETTER CHOICE.**

**SMC**  
PRESS ACTIVE SPLITTER

ON  
RACK



**16 OUTPUTS**  
REF: PT13376



**24 OUTPUTS**  
REF: PT13377



**32 OUTPUTS**  
REF: PT13378

ON  
WALLS



**16 OUTPUTS**  
REF: PT13831



**24 OUTPUTS**  
REF: PT13832



**32 OUTPUTS**  
REF: PT13833

ON  
BRIEFCASE



**16 OUTPUTS**  
REF: PT12436



**24 OUTPUTS**  
REF: PT12437



**32 OUTPUTS**  
REF: PT12438

## SIGNAL AMPLIFICATION AND EXTREME ISOLATION

The Pinanson SMC splitter guaranties an extreme isolation in each of the output channels. This splitter has the possibility of amplifying the input signal and this way it can compensates the signal distribution. Each signal is galvanically isolated through high quality transformers in a way that no noise interferes among the outputs.

## TEST & COMPARISON

The Pinanson SMC Splitter offers:

- 1 - Input test led vumeter, (permanent).
- 2 - Output test led vumeter, (pressing switch).  
This test can be done also with headphones.
- 3 - Desired output signal adjustable by potentiometer.



[PINANSON.COM](http://PINANSON.COM)

Pinanson, S.L. Avda.constitucion, 40, Mondéjar, Guadalajara, 19110, Spain  
Tel: +34 949 38 54 44 Fax: +34 949 38 56 43  
[pinanson@pinanson.com](mailto:pinanson@pinanson.com)

